


# Lytecaster Recessed Downlighting **300MRSPX**



Ceiling Opening: 3-3/4" (95mm)

Complete fixture consists of Reflector Trim & Remodeler. Select each separately.

Remodeler	Opening	Reflector Trim
300MRSPX	3-3/4 (95mm)	Accepts all 3-3/4 (95mm) 300X Series trims; See Reflector Trim specification sheets.

## Features

- Channel:** Ideal for retrofit installation. Bends at the thinner section to ease installation. Permits wiring from below the ceiling.
- Socket:** Porcelain body. Two-pin (GX5.3 base). Pre-wired with 18 ga. Teflon 250° leads to junction box.
- Thermal Protector:** Meets CSA/UL requirements. Insulation, if used, must be kept 3" (76mm) away from luminaire sides and junction box.
- Potted Transformer:** 50VA Magnetic, 120 volts primary, nominal 12 volt secondary, class "H". Can be removed easily. Fully encapsulated in epoxy resin inside aluminum casing.
- Junction Box:** 3-1/2 po (89mm) x 2-1/2 po (64mm) x 2 po (51mm) satin coated steel 20 ga. CSA certified for maximum of 4 No. 12 ga., 90°C through branch wiring. With two (2) 7/8" (22mm) integral pryouts. Easy access from both sides with two hinged junction box covers held in closed position with snap-on spring.
- BX Cable:** Bends down to make easier the installation.
- Sound insulation gasket, absorbs part of the vibrations.**

## Dimming

Dimming controls: Use only dimmers specifically designed for use with transformers, like Lightolier Onset series, Sunrise series LV or VA dimmers, or any Lightolier Controls dimming system.

## Labels

CSA, UL  
Rated for Damp or Wet location depending on trim used.

Job Information	Type:
<b>Job Name:</b>	
<b>Cat. No.:</b>	
<b>Lamp(s):</b>	
<b>Notes:</b>	