



Simply beautiful, affordable LED light

When all you need is light, this Philips everyday A19 LED delivers long life, energy savings, soft white light and contains no mercury. This 8.5W LED can replace a standard 60W incandescent and can last 10 years*.

Everyday LED

- A simple LED for everyday use

Instant on

- Instant On

Lasts 10 years

- Lasts 10 years*

Reduces energy costs

- Reduces energy costs

Similar to Incandescent

- Similar shape and size as a standard incandescent A19

Philips LED
Bulb

8.5 W (60 W)

Medium Screw base
Soft White
Non-dimmable



046677455507



PHILIPS

Bulb
8.5 W (60 W) Medium Screw base, Soft White, Non-dimmable

046677455507

Highlights

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Easily replaces incandescent



This bulb is an easy switch from standard incandescent A19 bulbs and delivers quality light for table and floor lamps, pendant fixtures and wall sconces.

Instant On



Just by turning the switch, the light is at full brightness. No slow starting or waiting.

Lasts 10 years*



Long life reduces the hassle of replacing bulbs so often.

Reduces energy costs



Estimated yearly energy cost for this LED bulb is \$1.02, based on 3 hours a day usage at 11¢/kWh.

Specifications

Bulb characteristics

- Base: Medium Screw base
- Dimmable: Non-dimmable
- Shape: Bulb
- Type: A19
- Indoor/Outdoor: Indoor
- Voltage: 120 V
- Shape Code: A19

Bulb dimensions

- Height: 2.4 inch
- Width: 4.2 inch
- Number of switch cycles: 0

Durability

- Lifetime of lamps: 10950 hour(s)
- Warm-up time to 60% light: Instant full light
- Average life (at 3 hrs/day): 10 year(s)

Light characteristics

- Light effect/finish: Soft White
- Color rendering index (CRI): 80
- Beam angle: 0 degree
- Color: Soft White
- Starting time: 0.2 s
- Color temperature: 2700 K

Power consumption

- Energy Star Certified: No
- Wattage: 8.5 W
- Wattage equivalent: 60 W
- Power consumption per 1000h: 0.0085 kW h
- Light output [lumen value]: 800



Issue date 2017-05-16

Version: 2.0.1

12 NC: 9290 011 35003

© 2017 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* 10 year means rated average life based on engineering testing and probability analysis where the lamp is used on average 3 hours/day, 7 days a week.