



Philips Halogen
Capsule

50W

G4
Clear

046677116149

Brilliant alternative to incandescents

Create bright accents indoors and along landscapes

Philips 50W indoor/outdoor halogen capsule provides bright sparkling accent light. An energy saving alternative to a 50W incandescent, it has no mercury and saves a lot of money.

Sparkling light

- Bright alternative to incandescent

Easy to use

- Instant On

PHILIPS

Capsule
50W G4, Clear

046677116149

Specifications

Bulb characteristics

- Shape: Capsule
- Type: T4
- Base: G4
- Voltage: 12 V

Power consumption

- Wattage: 50 W

Light characteristics

- Application: Accent light
- Color rendering index (CRI): 100
- Color temperature: 2800 K
- Light output: 700 lumen
- Light effect/finish: Clear

Durability

- Average life (at 2.7 hrs/day): 2 year(s)
- Lifetime of lamps: 2000 hour(s)

Highlights

Instant On

Just by turning the switch, your room is at full brightness. No slow starting or waiting.

Alternative to incandescent

This halogen light bulb provides a bright, sparkling light that is ideal for decorative fixtures and creating drama in your décor.



Issue date 2016-10-21

Version: 1.0.4

12 NC: 9240 620 17184

© 2016 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

* 2.7 years means rated average life based on engineering testing and probability analysis where the bulb is used on average 3 hours/day, 7 days a week.