



Philips Halogen
Linear

300 W

RSC base
Clear
Dimmable

067805011822

Brilliant alternative to incandescents

Make work spaces brighter with white light

Philips 300W dimmable halogen linear light bulb provides bright light for work and security tasks. An efficient alternative to 300W incandescents, it has no mercury and saves a lot of money.

Easy to use

- Dimmable***
- Instant On

PHILIPS

Linear
300 W RSC base, Clear, Dimmable

067805011822

Specifications

Bulb characteristics

- Shape: Linear
- Type: T3
- Base: RSC
- Voltage: 110-120 V
- Dimmable

Power consumption

- Wattage: 300 W

Light characteristics

- Application: Extra brightness
- Color rendering index (CRI): 100
- Color temperature: 2900 K
- Light output: 5000 lumen

Durability

- Average life (at 2.7 hrs/day): 2 year(s)
- Lifetime of lamps: 2000 hour(s)

Highlights

Dimmable***

This lamp can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels.

Instant On

Just by turning the switch, your room is at full brightness. No slow starting or waiting.



Issue date 2016-10-21

Version: 1.0.3

12 NC: 9247 352 34596

© 2016 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

***2.7 years means rated average life based on engineering testing and probability analysis where the lamp is used on average 3 hours/day, 7 days a week.