



Philips Halogen
Linear

150W

RSC base
Clear
Dimmable

046677116125

Brilliant alternative to incandescents

Make work spaces brighter with white light

Philips 150W dimmable halogen linear light bulb provides bright light for work and security tasks. An efficient alternative to 150W incandescents, it has no mercury and saves a lot of money.

Natural light

- Bright alternative to incandescent

Easy to use

- Dimmable***
- Instant On

PHILIPS

Linear
150W RSC base, Clear, Dimmable

046677116125

Specifications

Bulb characteristics

- Shape: Linear
- Type: T3
- Base: RSC
- Voltage: 110-120 V
- Dimmable

Power consumption

- Wattage: 150 W

Light characteristics

- Application: Extra brightness

- Color rendering index (CRI): 100
- Color temperature: 2730 K
- Light output: 2400 lumen
- Light effect/finish: Clear

Durability

- Average life (at 2.7 hrs/day): 3 year(s)
- Lifetime of lamps: 3000 hour(s)

Bulb dimensions

- Height: 3.11 inch
- Width: 0.38 inch

Highlights

Dimmable***

This lamp can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels.

Alternative to incandescent

This EcoVantage halogen light bulb provides beautiful light similar to natural daylight, ideal for enhancing your home.

Instant On

Just by turning the switch, your room is at full brightness. No slow starting or waiting.



Issue date 2016-10-21

Version: 2.1.4

12 NC: 9245 023 34590

© 2016 Philips Lighting Holding B.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Philips Lighting Holding B.V. or their respective owners.

www.philips.com

***2.7 years means rated average life based on engineering testing and probability analysis where the lamp is used on average 3 hours/day, 7 days a week.