

LED11WA19/300/840K-DIM-G5



Description 4000K LED LiteSpan A19 Omni-Directional 300 Degree Beam, 11W - 1100lm, Dimmable, 2BD E26

Ordering Code 08916

UNSPSC Code 39112102

Specifications

Voltage Rating	120
Voltage Type	AC/DC
Watts	11
Amps	0.1
mA	100
Lumens per Watt	100
Base Type	Medium Screw (E26)
Bulb Type	A-19
MOL in/mm	4.49/114
MOD in/mm	2.5/63.5
Lumens	1100
CT deg K	4000
CRI	80+
Beam Angle	300
Rated Life	25,000
Ambient Operating Temp Range	-20° C (-4° F) to 40° C (104° F)

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335