

## Eaton 10250T pushbutton

10250T476

UPC:782113226064

### Dimensions:

- **Height:** 1.38 IN
- **Length:** 3.3 IN
- **Width:** 2.4 IN

**Weight:** .25 LB

**Notes:** Contact blocks 10250T55 and 10250T57 cannot be used with this operator

### Warranties:

- 1 year

### Specifications:

- **Application:** Pushbutton
- **Special Features:** 10250T series
- **Type:** 30.5 mm Heavy-Duty Watertight/Oiltight
- **Illumination:** Illuminated
- **Light Unit Type:** Incandescent, full voltage
- **Light Unit Voltage:** 24 Vac/dc
- **Number Of Positions:** Three-position
- **Operating Mode:** Momentary push and pull, maintained intermediate
- **Size:** 30.5 mm
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

### Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T476](#)

### Certifications:

- CSA Certified
- UL Listed

### Product compliance:

- CE Marked



