

13 FOOT STANDOUT



IMPACT RESISTANT HOUSING

OVER-MOLDED WITH A SOFT TOUCH FINISH FOR EXCELLENT GRIP — STANDS UP TO JOBSITE DEMANDS




**TOUGH
BLADE**

HEAVY-DUTY, TOUGH,

DURABLE NYLON-COATING

PROTECTS BLADE PRINTING AND DELIVERS LONGER BLADE LIFE



CONDUIT BENDING TABLE AND 3-PHASE

LAYOUT GUIDE PRINTED ON BACK-SIDE OF TAPE FOR CONVENIENCE





TETHER
CAPABLE

STRONG MAGNETIC DOUBLE-HOOK
ATTACHES TO CONDUIT AND STEEL
STUDS. DOUBLE-HOOK ALLOWS FOR
VIEWING THE MEASUREMENT SCALES
PRINTED ON FRONT OR BACK OF TAPE



RETRACTION SPEED BRAKE CONTROLS
BLADE SPEED AND PROTECTS FINGERS
FROM TOUCHING BLADE

**UNCLUTTERED,
EASY-TO-READ
BOLD LINES**
MARKED ON BLADE
EVERY 1/8-INCH

3-PHASE TABLE	120/240V	277/480V
A = Black	1	2
B = Red	3	4
C = Blue	5	6
A = Brown	7	8
B = Orange	9	10
C = Yellow	11	12
	13	14
	15	16
	17	18
	19	20

PERFORMANCE AND DURABILITY EXPECTED BY PROFESSIONAL TRADESPEOPLE



Cat. No.	UPC 0-92644+	Blade Length	Hook	Magnetic	Measurement Scale	Tape Print
9216	69266-6	16' (4.9m)	Double	Yes	Imperial	Double-sided
9125	69267-3	25' (7.6m)	Single	No	Imperial	One-Sided
9225	69269-7	25' (7.6m)	Double	Yes	Imperial	Double-sided
9230	69272-7	30' (9.1m)	Double	Yes	Imperial	Double-sided
9375	69271-0	7.5m (24.6')	Double	Yes	Metric and Imperial	Double-sided



*Visit www.kleintools.com for safety warnings. Failure to follow all instructions and warnings may result in personal injury.
† CE applies to #9375 only.
US Patent D803711

Tape Measure Holders



5195



5196



5195TT



5707



5712

Holder Cat. No.	UPC 0-92644+	Description	Fits Tape Measures
5195	55078-2	Medium Leather Pouch	9216
5196	55092-8	Large Leather Pouch	9125, 9225, 9375, 9230
5195TT	55537-4	Tape Measure Holder With Ring	9216
5707	55167-3	Nylon Tape Measure Clip/Holder	9216, 9125, 9225, 9375, 9230
5712	55131-4	Nylon Pouch	9216, 9125, 9225, 9375, 9230



See our complete line of Levels & Measuring Tools

www.kleintools.com



© 2019 Klein Tools, Inc.
Lincolnshire, IL 60069
82889 Rev. 08/19 A