



S39674

54W/LED/HID/4000K/100-277V/EX39
54 watt - LED HID Replacement; 4000K; Mogul extended base;
100-277 volts

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP64 rated
- For outdoor & indoor use
- High-bay / Low-bay / Post-top
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- cULus listed

Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V
- Built in Surge Protection: 4KV

Shatter resistant materials, acceptable for use in food prep areas



S39674

Minimum Compartment Size		
Length	Width	Depth
8 inch	8 inch	15.75 inch

Optional Accessories

- In-line surge protector [80-929](#)
- Mog to med socket reducer (rated up to 250V) [92-406](#)

Item Number	Product Line	UPC	Input Voltage	Watts	Operating Frequency	Incandescent Equivalent	Fluorescent Equivalent
-------------	--------------	-----	---------------	-------	---------------------	-------------------------	------------------------

S39674	Hi-Pro	045923306747	100 - 277	54	50/60Hz	300W	85W	
HID Equivalent	Base	ANSI Base	Lamp Code		Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches
250W	Mogul Extended	EX39	54W/LED/HID/4000K/100-277V/EX39		Non-Dimmable	White	9-1/32"	3-11/32"
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature		Pack
7560	50000	4000	Cool White	80	300	-20C (-4F) to a maximum of +65C (+149F)		12
Package Type	CEC Status	DLC ID:	Material	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty	
Box	Lawful for sale in California	LUH2DVRZ8XC DLC Search	Aluminum	Yes	Yes	cULus - Damp Location Rated	5 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

