

# Miniature Circuit Breaker ST 200 M

## Ordering data characteristic B



Number of poles	Rated current I <sub>n</sub> [A]	Type code	Order code	Weight per PCE [kg]	Packing unit [PCE]
1	0.5	ST201M-B0,5	2CDS271334R0985	0.115	10
	1.6	ST201M-B1,6	2CDS271334R0975	0.115	10
	1	ST201M-B1	2CDS271334R0015	0.115	10
	2	ST201M-B2	2CDS271334R0025	0.115	10
	3	ST201M-B3	2CDS271334R0035	0.115	10
	4	ST201M-B4	2CDS271334R0045	0.115	10
	5	ST201M-B5	2CDS271334R0055	0.115	10
	6	ST201M-B6	2CDS271334R0065	0.115	10
	7	ST201M-B7	2CDS271334R0075	0.115	10
	8	ST201M-B8	2CDS271334R0085	0.115	10
	10	ST201M-B10	2CDS271334R0105	0.115	10
	13	ST201M-B13	2CDS271334R0135	0.115	10
	15	ST201M-B15	2CDS271334R0155	0.115	10
	16	ST201M-B16	2CDS271334R0165	0.115	10
	20	ST201M-B20	2CDS271334R0205	0.115	10
	25	ST201M-B25	2CDS271334R0255	0.115	10
	30	ST201M-B30	2CDS271334R0305	0.115	10
	32	ST201M-B32	2CDS271334R0325	0.115	10
	35	ST201M-B35	2CDS271334R0355	0.115	10
	40	ST201M-B40	2CDS271334R0405	0.115	10
50	ST201M-B50	2CDS271334R0505	0.115	10	
60	ST201M-B60	2CDS271334R0605	0.115	10	
63	ST201M-B63	2CDS271334R0635	0.115	10	
1+N	0.5	ST201M-B1,6NA	2CDS271335R0975	0.230	5
	1.6	ST201M-B0,5NA	2CDS271335R0985	0.230	5
	1	ST201M-B1NA	2CDS271335R0015	0.230	5
	2	ST201M-B2NA	2CDS271335R0025	0.230	5
	3	ST201M-B3NA	2CDS271335R0035	0.230	5
	4	ST201M-B4NA	2CDS271335R0045	0.230	5
	5	ST201M-B5NA	2CDS271335R0055	0.230	5
	6	ST201M-B6NA	2CDS271335R0065	0.230	5
	7	ST201M-B7NA	2CDS271335R0075	0.230	5
	8	ST201M-B8NA	2CDS271335R0085	0.230	5
	10	ST201M-B10NA	2CDS271335R0105	0.230	5
	13	ST201M-B13NA	2CDS271335R0135	0.230	5
	15	ST201M-B15NA	2CDS271335R0155	0.230	5
	16	ST201M-B16NA	2CDS271335R0165	0.230	5
	20	ST201M-B20NA	2CDS271335R0205	0.230	5
	25	ST201M-B25NA	2CDS271335R0255	0.230	5
	30	ST201M-B30NA	2CDS271335R0305	0.230	5
	32	ST201M-B32NA	2CDS271335R0325	0.230	5
	35	ST201M-B35NA	2CDS271335R0355	0.230	5
	40	ST201M-B40NA	2CDS271335R0405	0.230	5
50	ST201M-B50NA	2CDS271335R0505	0.230	5	
60	ST201M-B60NA	2CDS271335R0605	0.230	5	
63	ST201M-B63NA	2CDS271335R0635	0.230	5	
2	0.5	ST202M-B0,5	2CDS272334R0985	0.230	5
	1.6	ST202M-B1,6	2CDS272334R0975	0.230	5
	1	ST202M-B1	2CDS272334R0015	0.230	5
	2	ST202M-B2	2CDS272334R0025	0.230	5
	3	ST202M-B3	2CDS272334R0035	0.230	5
	4	ST202M-B4	2CDS272334R0045	0.230	5
	5	ST202M-B5	2CDS272334R0055	0.230	5
	6	ST202M-B6	2CDS272334R0065	0.230	5
	7	ST202M-B7	2CDS272334R0075	0.230	5
	8	ST202M-B8	2CDS272334R0085	0.230	5
	10	ST202M-B10	2CDS272334R0105	0.230	5
	13	ST202M-B13	2CDS272334R0135	0.230	5
	15	ST202M-B15	2CDS272334R0155	0.230	5
	16	ST202M-B16	2CDS272334R0165	0.230	5
	20	ST202M-B20	2CDS272334R0205	0.230	5
	25	ST202M-B25	2CDS272334R0255	0.230	5
	30	ST202M-B30	2CDS272334R0305	0.230	5
	32	ST202M-B32	2CDS272334R0325	0.230	5
	35	ST202M-B35	2CDS272334R0355	0.230	5
	40	ST202M-B40	2CDS272334R0405	0.230	5
50	ST202M-B50	2CDS272334R0505	0.230	5	
60	ST202M-B60	2CDS272334R0605	0.230	5	
63	ST202M-B63	2CDS272334R0635	0.230	5	

# Miniature Circuit Breaker ST 200 M

Ordering data characteristic B



Number of poles	Rated current I <sub>n</sub> [A]	Type code	Order code	Weight per PCE [kg]	Packing unit [PCE]
3	0.5	ST203M-B0,5	2CDS273334R0985	0.345	1
	1.6	ST203M-B1,6	2CDS273334R0975	0.345	1
	1	ST203M-B1	2CDS273334R0015	0.345	1
	2	ST203M-B2	2CDS273334R0025	0.345	1
	3	ST203M-B3	2CDS273334R0035	0.345	1
	4	ST203M-B4	2CDS273334R0045	0.345	1
	5	ST203M-B5	2CDS273334R0055	0.345	1
	6	ST203M-B6	2CDS273334R0065	0.345	1
	7	ST203M-B7	2CDS273334R0075	0.345	1
	8	ST203M-B8	2CDS273334R0085	0.345	1
	10	ST203M-B10	2CDS273334R0105	0.345	1
	13	ST203M-B13	2CDS273334R0135	0.345	1
	15	ST203M-B15	2CDS273334R0155	0.345	1
	16	ST203M-B16	2CDS273334R0165	0.345	1
	20	ST203M-B20	2CDS273334R0205	0.345	1
	25	ST203M-B25	2CDS273334R0255	0.345	1
	30	ST203M-B30	2CDS273334R0305	0.345	1
	32	ST203M-B32	2CDS273334R0325	0.345	1
	35	ST203M-B35	2CDS273334R0355	0.345	1
	40	ST203M-B40	2CDS273334R0405	0.345	1
50	ST203M-B50	2CDS273334R0505	0.345	1	
60	ST203M-B60	2CDS273334R0605	0.345	1	
63	ST203M-B63	2CDS273334R0635	0.345	1	
3+N	0.5	ST203M-B1,6NA	2CDS273335R0975	0.460	1
	1.6	ST203M-B0,5NA	2CDS273335R0985	0.460	1
	1	ST203M-B1NA	2CDS273335R0015	0.460	1
	2	ST203M-B2NA	2CDS273335R0025	0.460	1
	3	ST203M-B3NA	2CDS273335R0035	0.460	1
	4	ST203M-B4NA	2CDS273335R0045	0.460	1
	5	ST203M-B5NA	2CDS273335R0055	0.460	1
	6	ST203M-B6NA	2CDS273335R0065	0.460	1
	7	ST203M-B7NA	2CDS273335R0075	0.460	1
	8	ST203M-B8NA	2CDS273335R0085	0.460	1
	10	ST203M-B10NA	2CDS273335R0105	0.460	1
	13	ST203M-B13NA	2CDS273335R0135	0.460	1
	15	ST203M-B15NA	2CDS273335R0155	0.460	1
	16	ST203M-B16NA	2CDS273335R0165	0.460	1
	20	ST203M-B20NA	2CDS273335R0205	0.460	1
	25	ST203M-B25NA	2CDS273335R0255	0.460	1
	30	ST203M-B30NA	2CDS273335R0305	0.460	1
	32	ST203M-B32NA	2CDS273335R0325	0.460	1
	35	ST203M-B35NA	2CDS273335R0355	0.460	1
	40	ST203M-B40NA	2CDS273335R0405	0.460	1
50	ST203M-B50NA	2CDS273335R0505	0.460	1	
60	ST203M-B60NA	2CDS273335R0605	0.460	1	
63	ST203M-B63NA	2CDS273335R0635	0.460	1	
4	0.5	ST204M-B0,5	2CDS274334R0985	0.460	1
	1.6	ST204M-B1,6	2CDS274334R0975	0.460	1
	1	ST204M-B1	2CDS274334R0015	0.460	1
	2	ST204M-B2	2CDS274334R0025	0.460	1
	3	ST204M-B3	2CDS274334R0035	0.460	1
	4	ST204M-B4	2CDS274334R0045	0.460	1
	5	ST204M-B5	2CDS274334R0055	0.460	1
	6	ST204M-B6	2CDS274334R0065	0.460	1
	7	ST204M-B7	2CDS274334R0075	0.460	1
	8	ST204M-B8	2CDS274334R0085	0.460	1
	10	ST204M-B10	2CDS274334R0105	0.460	1
	13	ST204M-B13	2CDS274334R0135	0.460	1
	15	ST204M-B15	2CDS274334R0155	0.460	1
	16	ST204M-B16	2CDS274334R0165	0.460	1
	20	ST204M-B20	2CDS274334R0205	0.460	1
	25	ST204M-B25	2CDS274334R0255	0.460	1
	30	ST204M-B30	2CDS274334R0305	0.460	1
	32	ST204M-B32	2CDS274334R0325	0.460	1
	35	ST204M-B35	2CDS274334R0355	0.460	1
	40	ST204M-B40	2CDS274334R0405	0.460	1
50	ST204M-B50	2CDS274334R0505	0.460	1	
60	ST204M-B60	2CDS274334R0605	0.460	1	
63	ST204M-B63	2CDS274334R0635	0.460	1	

# Miniature Circuit Breaker ST 200 M

Ordering data characteristic C



Number of poles	Rated current I <sub>n</sub> [A]	Type code	Order code	Weight per PCE [kg]	Packing unit [PCE]
1	0.5	ST201M-C0,5	2CDS271334R0984	0.115	10
	1.6	ST201M-C1,6	2CDS271334R0974	0.115	10
	1	ST201M-C1	2CDS271334R0014	0.115	10
	2	ST201M-C2	2CDS271334R0024	0.115	10
	3	ST201M-C3	2CDS271334R0034	0.115	10
	4	ST201M-C4	2CDS271334R0044	0.115	10
	5	ST201M-C5	2CDS271334R0054	0.115	10
	6	ST201M-C6	2CDS271334R0064	0.115	10
	7	ST201M-C7	2CDS271334R0074	0.115	10
	8	ST201M-C8	2CDS271334R0084	0.115	10
	10	ST201M-C10	2CDS271334R0104	0.115	10
	13	ST201M-C13	2CDS271334R0134	0.115	10
	15	ST201M-C15	2CDS271334R0154	0.115	10
	16	ST201M-C16	2CDS271334R0164	0.115	10
	20	ST201M-C20	2CDS271334R0204	0.115	10
	25	ST201M-C25	2CDS271334R0254	0.115	10
	30	ST201M-C30	2CDS271334R0304	0.115	10
	32	ST201M-C32	2CDS271334R0324	0.115	10
	35	ST201M-C35	2CDS271334R0354	0.115	10
	40	ST201M-C40	2CDS271334R0404	0.115	10
	50	ST201M-C50	2CDS271334R0504	0.115	10
	60	ST201M-C60	2CDS271334R0604	0.115	10
	63	ST201M-C63	2CDS271334R0634	0.115	10
1+N	0.5	ST201M-C1,6NA	2CDS271335R0974	0.230	5
	1.6	ST201M-C0,5NA	2CDS271335R0984	0.230	5
	1	ST201M-C1NA	2CDS271335R0014	0.230	5
	2	ST201M-C2NA	2CDS271335R0024	0.230	5
	3	ST201M-C3NA	2CDS271335R0034	0.230	5
	4	ST201M-C4NA	2CDS271335R0044	0.230	5
	5	ST201M-C5NA	2CDS271335R0054	0.230	5
	6	ST201M-C6NA	2CDS271335R0064	0.230	5
	7	ST201M-C7NA	2CDS271335R0074	0.230	5
	8	ST201M-C8NA	2CDS271335R0084	0.230	5
	10	ST201M-C10NA	2CDS271335R0104	0.230	5
	13	ST201M-C13NA	2CDS271335R0134	0.230	5
	15	ST201M-C15NA	2CDS271335R0154	0.230	5
	16	ST201M-C16NA	2CDS271335R0164	0.230	5
	20	ST201M-C20NA	2CDS271335R0204	0.230	5
	25	ST201M-C25NA	2CDS271335R0254	0.230	5
	30	ST201M-C30NA	2CDS271335R0304	0.230	5
	32	ST201M-C32NA	2CDS271335R0324	0.230	5
	35	ST201M-C35NA	2CDS271335R0354	0.230	5
	40	ST201M-C40NA	2CDS271335R0404	0.230	5
	50	ST201M-C50NA	2CDS271335R0504	0.230	5
	60	ST201M-C60NA	2CDS271335R0604	0.230	5
	63	ST201M-C63NA	2CDS271335R0634	0.230	5
2	0.5	ST202M-C0,5	2CDS272334R0984	0.230	5
	1.6	ST202M-C1,6	2CDS272334R0974	0.230	5
	1	ST202M-C1	2CDS272334R0014	0.230	5
	2	ST202M-C2	2CDS272334R0024	0.230	5
	3	ST202M-C3	2CDS272334R0034	0.230	5
	4	ST202M-C4	2CDS272334R0044	0.230	5
	5	ST202M-C5	2CDS272334R0054	0.230	5
	6	ST202M-C6	2CDS272334R0064	0.230	5
	7	ST202M-C7	2CDS272334R0074	0.230	5
	8	ST202M-C8	2CDS272334R0084	0.230	5
	10	ST202M-C10	2CDS272334R0104	0.230	5
	13	ST202M-C13	2CDS272334R0134	0.230	5
	15	ST202M-C15	2CDS272334R0154	0.230	5
	16	ST202M-C16	2CDS272334R0164	0.230	5
	20	ST202M-C20	2CDS272334R0204	0.230	5
	25	ST202M-C25	2CDS272334R0254	0.230	5
	30	ST202M-C30	2CDS272334R0304	0.230	5
	32	ST202M-C32	2CDS272334R0324	0.230	5
	35	ST202M-C35	2CDS272334R0354	0.230	5
	40	ST202M-C40	2CDS272334R0404	0.230	5
	50	ST202M-C50	2CDS272334R0504	0.230	5
	60	ST202M-C60	2CDS272334R0604	0.230	5
	63	ST202M-C63	2CDS272334R0634	0.230	5