

**M12™ Heated AXIS™ Vest Kit**

Black 303B-21 (S - 3X)\*  
303B-20 Vest-Only



**Specifications:**

Heat Zones	2 (Chest, Back)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 6 Hours
Outer Material	AXIS™ Ripstop Polyester
Wind / Water Resistant	Yes
Washer / Dryer Safe	Yes

**Includes:** (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, M12™ Battery Holder, Charger



**M12™ Women's Heated AXIS™ Vest Kit**

Black 333B-21 (S - 2X)\*  
333B-20 Vest-Only



**Specifications:**

Heat Zones	2 (Chest, Back)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 6 Hours
Outer Material	AXIS™ Ripstop Polyester
Wind / Water Resistant	Yes
Washer / Dryer Safe	Yes

**Includes:** (1) M12™ REDLITHIUM™ CP1.5 Battery Pack, M12™ Battery Holder, Charger

**USB Rechargeable Heated Gloves Kit**

561-21 (M - XL)\*

**Specifications:**

Heat Zones	2 (Fingers, Back of Hand)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 6 Hours
Material	GRIDIRON™ Ripstop Polyester
Wind / Water Resistant	Yes



**Includes:** (2) REDLITHIUM™ USB Battery Packs, (2) USB Charger/Controllers, Heavy Duty Cord and Wall Plug

**M12™ Heated Gear Accessory**

Compatible with all M12™ Heated Gear  
49-24-2301 M12™ Heated Jacket 12V DC Plug Adapter



**M12™ Power Source**

49-24-2310

**Specifications:**

2.1 Amp USB Port	Universal Charging for Smartphones, Tablets and Other Portable Electronic Devices
On-Board Fuel Gauge	Yes
Powered By	All M12™ Batteries



Battery Sold Separately

Powers all MILWAUKEE® M12™ Heated Gear



**Related Accessory:**

48-59-1201 M12™ Compact Charger and Power Source

**M18™ / M12™ Wireless Jobsite Speaker**

2891-20 Tool-Only

**Specifications:**

Modes	Bluetooth®, AUX (Cable Not Included)
Bluetooth® Range	100 ft
USB Charging Port	2.1A USB Charging Port for External Devices
Powered By	All M18™ and M12™ Batteries



Battery and Charger Sold Separately

**Includes:** AC Adapter

**M12™ Jobsite Radio**

2590-20 Tool-Only

**Specifications:**

Modes	AM, FM, AUX
Tuner	Digital Processor w/ 10 Station Presets
Powered By	All M12™ Batteries, AC Adapter



Battery and Charger Sold Separately

**Includes:** Auxiliary Input Cord, AC Adapter, (2) AAA Batteries (For Memory Backup)

**M12™ Wireless Jobsite Speaker**

2592-20 Tool-Only

**Specifications:**

Modes	Bluetooth®, AUX (Cable Not Included)
Bluetooth® Range	30 ft Range
USB Charging Port	2.1A USB Charging Port for External Devices
Powered By	All M12™ Batteries



Battery and Charger Sold Separately

**M12™ Compact Inflator Kit**

2475-21XC (2475-20 Tool-Only)

**Specifications:**

PSI Rating	0 - 120 PSI
Hose Length	26"
Gauge Accuracy	+/- 3%
Duty Cycle	50% at 10 Minutes On and 10 Minutes Off
Height	7.5"
Weight	2.2 lbs



**Includes:** (1) M12™ REDLITHIUM™ XC4.0 Battery Pack, (4) Attachments (Ball Inflation Needle, Presta Chuck, Inflator Nozzle, Schrader Chuck), Charger

**M12™ Compact Vacuum**

0850-20 Tool-Only

**Specifications:**

Air Volume	33 CFM
Suction (H <sub>2</sub> O)	14.5"
Run-Time (XC4.0)	Up to 29 mins
Inlet Diameter	1-1/4"
Weight	2.3 lbs



Battery and Charger Sold Separately

**Includes:** Utility Nozzle, Extension Wand, Crevice Tool, Filter Assembly

**Related Accessory:**

49-90-1950 Filter

**M12™ REDLITHIUM™ CP2.0 System Starter Kit**

48-59-2420

**Includes:** (1) M12™ REDLITHIUM™ CP2.0 Battery Pack, Charger



**M18™ & M12™ Rapid Charger**

48-59-1808

**Specifications:**

Compatibility	All M18™ and M12™ Batteries
Charge Sequence	Sequential (First In, First Charged)
Charge Speed	Charges Individual Batteries up to 40% Faster
On-Board Indicator Light	Yes
Integrated Hang-Holes	Yes
Cell Voltage Monitoring	Yes



Batteries Sold Separately

**M18™ & M12™ Multi-Voltage Charger**

48-59-1812

**Specifications:**

Compatibility	All M18™ and M12™ Batteries
Charge Sequence	Sequential (First In, First Charged)
Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



Batteries Sold Separately

**M18™ & M12™ Vehicle Charger**

48-59-1810

**Specifications:**

Compatibility	All M18™ and M12™ Batteries
Charge Sequence	Sequential (First In, First Charged)
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



Batteries Sold Separately

**M12™ Four Bay Sequential Charger**

48-59-1204

**Specifications:**

Compatibility	All M12™ Batteries
Charge Sequence	Sequential (First In, First Charged)
Integrated Hang-Holes	Yes
Skip Button	Manually Designate which Battery Charges First
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



Batteries Sold Separately

**M18™ & M12™ Rapid Charge Station**

48-59-1807

**Specifications:**

Compatibility	All M18™ and M12™ Batteries
Charge Sequence	Charges 3 Batteries Simultaneously
Charge Speed	Charges Individual Batteries up to 40% Faster
Capacity	Holds (3) M18™ and (3) M12™ Batteries
Integrated Hang-Holes	Yes
Cell Voltage Monitoring	Yes
Pass-Through Plug	Yes



Batteries Sold Separately



**M12™ Charger**

48-59-2401

**Specifications:**

Compatibility	All M12™ Batteries
Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



Battery Sold Separately