

GU10 Indoor Flood



Part #	Description (HAL Wattage)	Bulb Shape	Bulb Base	Colour (Temp.)	Beam Degree	Lumens	Hours	Dim.	E-Star
213454	HAL 35W 6Pk (35W)	GU10	GU10	CLR (2800K)	35°	265	2000	Y	
213462	HAL 50W 6Pk (50W)	GU10	GU10	CLR (2800K)	35°	430	2000	Y	
218297	HAL 50W 12Pk (50W)	GU10	GU10	CLR (2800K)	35°	430	2000	Y	

MR Indoor Flood



Part #	Description (HAL Wattage)	Bulb Shape	Bulb Base	Colour (Temp.)	Beam Degree	Lumens	Hours	Dim.	E-Star
127738	HAL 20W (20W)	MRC11	G4	CLR (2700K)	28°	300	4000	Y	
127746	HAL 35W (35W)	MRC11	G4	CLR (2700K)	28°	750	4000	Y	
151209	HAL 50W 3PK (50W)	MRC16	GU5.3	CLR (2800K)	35°	870	2000	Y	
162479	HAL 20W (20W)	MRC16	GU5.3	CLR (2700K)	28°	260	2000	Y	
162487	HAL 35W (35W)	MRC16	GU5.3	CLR (2700K)	28°	560	2000	Y	
278846	HAL 50W Xenon 3Pk (50W)	MRC16	Med. Base	CLR (3000K)	35°	540	2000	Y	