



## ENERGY STAR CERTIFIED Light Bulbs

### Philips LED : 9290013583

#### Specifications

<b>ENERGY STAR Partner:</b>	Signify North America Corporation
<b>Brand Name:</b>	Philips LED
<b>Model Number:</b>	9290013583
<b>Product Finder Bulb Type:</b>	General Purpose Replacement
<b>Base Type:</b>	E26 (Medium)
<b>Lamp Category:</b>	Omnidirectional
<b>Technology:</b>	LED
<b>Warranty (years):</b>	3
<b>Energy Used (watts):</b>	9.5
<b>Efficacy (lumens/watt):</b>	84.2
<b>Wattage Equivalency (watts):</b>	60
<b>Maximum Overall Length (mm):</b>	109.5
<b>Maximum Overall Diameter (mm):</b>	61.3
<b>Life (hrs):</b>	15000
<b>Brightness (lumens):</b>	800
<b>Power Factor:</b>	0.9
<b>Light Appearance (Kelvin):</b>	2700
<b>Color Quality (CRI):</b>	82
<b>R9:</b>	9
<b>Connected Lamp:</b>	No
<b>Dimmable:</b>	Dimmable
<b>Dims Down to %:</b>	20.0
<b>Three Way:</b>	No
<b>Lamp Rated for Enclosed Fixtures:</b>	No
<b>Special Features:</b>	Damp Location Rated,Use With Timers,Not for Use in Recessed Fixtures,Use With Photo and/or Motion Sensors
<b>Date Qualified:</b>	2017-01-24
<b>Date Available on Market:</b>	2017-01-23
<b>Markets:</b>	Canada
<b>ENERGY STAR Certified:</b>	Yes

#### Additional Model Information

„Retail Number: 9.5A19/LED/827 DIM 120V 1/8 (471508)

**Captured On:**  
07/26/2019