



ENERGY STAR CERTIFIED Light Bulbs

PhilipsLED : 9290013582

Specifications

ENERGY STAR Partner:	Signify North America Corporation
Brand Name:	PhilipsLED
Model Number:	9290013582
Product Finder Bulb Type:	Reflector (Flood/Spot)
Base Type:	GU10
Lamp Category:	Directional
Technology:	LED
Warranty (years):	5
Energy Used (watts):	4.5
Efficacy (lumens/watt):	84.4
Wattage Equivalency (watts):	50
Maximum Overall Length (mm):	47.0
Maximum Overall Diameter (mm):	49.8
CBCP:	610
Beam Angle:	35
Life (hrs):	25000
Brightness (lumens):	380
Power Factor:	0.9
Light Appearance (Kelvin):	2700
Color Quality (CRI):	81
R9:	7
Connected Lamp:	No
Dimmable:	Dimmable
Dims Down to %:	20.0
Three Way:	No
Lamp Rated for Enclosed Fixtures:	Yes
Special Features:	Use With Timers,Dim to Warm,Damp Location Rated,Use With Photo and/or Motion Sensors,Recessed Fixtures
Date Qualified:	2017-05-24
Date Available on Market:	2017-05-16
Markets:	United States, Canada
ENERGY STAR Certified:	Yes

Additional Model Information

,9290013582,4.5GU10/AMB/2200-2700/GL/DIM BC 3PK (474544);4.5GU10/EDP/822-27/F35/CLA/GL/DIM BC 1PK (471557);4.5GU10/EDP/822-27/F35/CLA/GL/DIM FB 1PK (471565);4.5GU10/EDP/822-27/F35/CLA/GL/DIM BC 1PK (471573)

Captured On:
07/26/2019