

DL010-024-200VD 0-10V Dimmable Driver

Description

Diffusion DL010-024-200VD is a 0-10V constant voltage dimmable driver.

Features

- Protection from short circuit, over current and over voltage
- IP67 waterproof, designed for indoors and outdoors
- Wiring junction boxes built in for line and load

Specifications

- Output Voltage : 24 VDC
- Output Current : 8.3A
- Dimming Functions : 0-10V
- Dimming Range : 0-100%

Driver Dimensions :

10.10" L x 3.10" W x 1.75" H
257mm L x 79mm W x 45mm H

Enclosure Dimensions :

16.13" L x 3.38" W x 2.25" H
410mm L x 86mm W x 57mm H

