



CT4 Series

400 AMP METER SOCKET 120/240 VOLT, Single Phase c/w circuit breaker

CATALOGUE #	TYPE	DESCRIPTION	DIMENSIONS (IN.)			WEIGHT
			H	W	D	
CT4-WS-BC	U/G	5 Jaw, c/w 400 AMP 65kA rated circuit breaker	42	26	8 ¹ / ₄	110 lbs.
CT4-WSOH-BC	O/H	5 Jaw, c/w 400 AMP 65kA rated circuit breaker	50	16	8 ¹ / ₄	68 lbs.
CT4PMK-WS		Accessories Pole Bracket for CT4-WS-BC				
CT4PMKWSOH		Pole Bracket for CT4-WSOH-BC				

- 400 Amp - 120/240 VOLT
- All in One Transformer Rated
- Combination meter socket & Siemens 400A 240V 65 KA breaker
- CSA enclosure 3R
- Load and line side terminations: tunnel type connectors, dual rated for 1 x 600 kcmil or 2 x 250 kcmil
- Provision for test switch (Supplied by Hydro)
- Provision for current transformer (Supplied by Hydro)
- Secondary circuit wiring not included (secondary circuit wired by Hydro)

KNOCKOUT CODE	CONDUIT SIZE
K	2", 2 ¹ / ₂ ", 3"
P	2", 2 ¹ / ₂ ", 3", 3 ¹ / ₂ ", 4"
AA	1 ¹ / ₂ "

