


Plug-In Outlet Center® Units

Plug-In Outlet Center® Units

Wiremold® Plug-In Outlet Center Units bring power safely and conveniently to wherever you need it. These units are ideal for use in a wide variety of settings, including relay racks and cabinets, laboratories, workshops, classrooms and offices.

Plug-In Outlet Center Units include rack mount, Cabinet-MATE, compact, 90 degree, deluxe control, industrial, and international units. Most units are available in both 15 and 20 Amp configurations.

Wiremold also offers extensive custom capabilities for Plug-In Outlet Center Units. Contact the factory for more information.



J08B0B (Front & Back)







UL207BC J06B0B20X-AM (Front)

FEATURES & BENEFITS

- User-ready outlets. Plug-In Outlet Center units provide power distribution in a portable, plug-in unit.
- Rugged construction. Durable 2" x 1 3/4" [44mm x 51mm] or 3 1/2" x 2" [89mm x 44mm] aluminum housing. Some Plug-In Outlet Center units are available with an impactresistant plastic housing.
- Space saving. Rack mount units fit standard 19" [482mm] relay racks. Compact 1U design takes up minimum space. 23" [584mm] units available, consult factory.
- Low profile. CabinetMATE units offer a narrow 1 1/2" x 1 3/16" [38mm x 20mm] aluminum housing.
- Aesthetically pleasing. Rack mount units have a black matte finish and a black cord. CabinetMATE, compact and industrial units have a gray finish and a black cord. Deluxe control and 20A units have a putty white finish and a black cord. Most units with a putty white finish have a putty white cord. Special Use units have a white finish and a white cord.

■ Flexible mounting. Each unit features one of four different mounting types. Each mounting method has been designed to optimize the performance of the product. Complete mounting hardware and installation instructions are included with every unit.

P6


- Cord properly rated to load requirements. 15A units have a 14/3 SJT cord and a NEMA 5-15P plug. 20A units have a 12/3 SJT cord and a NEMA 5-20P or NEMA L5-20P plug.
- Lighted switch. Most units have lighted on/off switch(es) to control power to the unit.
- Resettable circuit breaker. Provides overload protection.
- Two-Year product warranty.
- UL and cUL Listed or Recognized. Units are UL and cUL Listed to UL1363 standards. Rack mount units are UL and cUL Recognized to UL1363 standards.

15A Rack Mount Plug-In Outlet Centers Ordering Information

Catalog No./Item

Description/Specifications

J08B0B J08B2B



Rack Mount Plug-In Outlet

Center - Eight rear outlets, lighted switch. Receptacles rotated 90° and 4 outlets spaced to accommodate transformers. 6' [1.8m] (J08B0B) or 15' [4.6m] (J08B2B) cord. Receptacle center-to-center 1 1/2" [38mm] and 2" [51mm].






J06B0B J06B2B **Rack Mount Plug-In Outlet** Center - Six rear outlets, lighted switch. 6' [1.8m] (J06B0B) or 15' [4.6m] (J08B2B) cord. Receptacle center-to-center1 1/2" [38mm].



J06B0BX J06B2BX



Rack Mount Plug-In Outlet Center - Six rear outlets. 6' [1.8m] (J06B0BX)or 15' [4.6m] (J06B2B) cord. Receptacle center-to-center 1 1/2" [38mm].



Catalog No./Item



Description/Specifications

Rack Mount Plug-In Outlet Center - Six front outlets, lighted switch. 6' [1.8m] (J60B0B) or 15' [4.6m] (J60B2B) cord. Receptacle center-to-center1 1/2" [38mm].



J60B0B-90 J60B2B-90



Rack Mount Plug-In Outlet Center - Six front outlets, lighted switch. Receptacles rotated 90°. 6' [1.8m] (J60B0B-90) or 15' [4.6m] (J60B2B-90) cord. Receptacle center-to-center 1 1/2" [38mm].



J24B0B J24B2B



Rack Mount Plug-In Outlet Center - Two front, four rear outlets. Lighted switch. 6' [1.8m] (J24B0B) or 15' [4.6m] (J24B2 B)cord. Receptacle center-to-center 1 1/2" [38mm].



20A Rack Mount Plug-In Outlet Centers Ordering Information

Catalog No./Item

Description/Specifications

J06B0B20 J06B2B20 **Rack Mount Plug-In Outlet** Center - Six 20A rear outlets, on/off switch. 6' [1.8m] (J06B0B20) or 15' [4.6m] (J06B2B20) cord. Receptacle center-to-center 1 1/2" [38mm].



J06B0B20X J06B2B20X

Rack Mount Plug-In Outlet Center - Six 20A rear outlets. 6' [1.8m] (J08B0B20X) or 15' [4.6m] (J06B0B20X) cord. Receptacle center-to-center 1 1/2" [38mm].





Description/Specifications

Rack Mount Plug-In Outlet Center - Six 20A front outlets,

on/off switch. 6' [1.8m] (J60B0B20) or 15' [4.6m] (J60B2B20) cord. Receptacle center-to-center 1 1/2" [38mm].

J60B0B20X J60B2B20X

Catalog No./Item

J60B0B20


J60B2B20



Rack Mount Plug-In Outlet Center - Six 20A front outlets. 6' [1.8m] (J60B0B20X) or 15' [4.6m] (J60B2B20X) cord. Receptacle center-to-center 1 1/2" [38mm].

J06B0B20X-AM

J60B0B (Front & Back)




Rack Mount Plug-In Outlet Center with Digital Ammeter -Digital LCD readout of current draw. Six 20A rear outlets. 6' [1.8m] cord. Receptacle centerto-center 1 1/2"[38mm].









J06B0B20X (Front & Back)

atalog No./Item	Description/Specifications		
3609ULBC 3609ULBD	CabinetMATE Plug-In Outlet Center – Nine outlets. 6' [1.8m] (3609ULBC) or 15' [4.6m] (3609ULBD) cord. Length 36" [914mm]. Receptacle center-to-center 3" [76mm].		
4810ULBC 4810ULBD	CabinetMATE Plug-In Outlet Center – Ten outlets. 6' [1.8m] (4810ULBC) or 15' [4.6m] (4810ULBD)cord. Length 48" [1.2m]. Receptacle center-to-center 4" [102mm].		
7011ULBC 7011ULBD	CabinetMATE Plug-In Outlet Center – Eleven outlets. 6' [1.8m] (7011ULBC) or 15' [4.6m] (7011ULBD) cord. Length 70" [1.8m]. Receptacle center-to-center 6" [152mm].		9 9 9
7712ULBC 7712ULBD	CabinetMATE Plug-In Outlet Center – Twelve outlets. 6' [1.8m] (7712ULBC) or 15' [4.6m] (7712ULBD) cord. Length 77" [2m]. Receptacle center-to-center 6" [152mm].		
	c UL) us	┚┈╢╢	
			4810ULBC/
		3609ULBC/	4810ULBD
		3609ULBD	

20A CabinetMATE Plug-In Outlet Centers Ordering Information **Description/Specifications** Catalog No./Item 2008ULBC20R CabinetMATE Plug-In Outlet 2008ULBD20R Center - Eight 20A outlets with 2008ULBC20R-TL* t-slots. 6' [1.8m] (2008ULBC20R, 2008ULBD20R-TL* 2008ULBC20R-TL) or 15' [4.6m] (2008ULBD20R, 2008ULBD20R-TL) cord. Length 20" [508mm]. Receptacle center-to-center 1 1/4" [32mm]. Units available with straight blade or NEMA L5-20P locking plug. 4810ULBC20R CabinetMATE Plug-In Outlet Center - Ten 20A outlets with 4810ULBD20R 4810ULBC20R-TL* t-slots. 6' [1.8m] (4810ULBC20R, 4810ULBD20R-TL* 4810ULBC20R-TL) or 15' [4.6m] (4810ULBD20R, 4810ULBD20R-TL) cord.Length 48" [1.2m]. Receptacle center-to-center 4" [102mm]. Units available with straight blade or NEMA L5-20P locking plug. 2008ULBC20R/ 2008ULBD20R 7011ULBC20R CabinetMATE Plug-In Outlet 7011ULBD20R Center - Eleven 20A outlets with 7011ULBC20R-TL* t-slots. 6' [1.8m] (7011ULBC20R, 7011ULBD20R-TL* 7011ULBC20R-TL) or 15' [4.6m] (7011ULBD20R, 7011ULBD20R-TL) cord. Length 70" [1.6m]. Receptacle center-to-center 6" [152mm]. Units available with straight blade or NEMA L5-20P locking plug. 4810ULBC20R/ c(UL)us 4810ULBD20R 7712ULBC20R CabinetMATE Plug-In Outlet 7712ULBD20R **Center –** Twelve 20A outlets with. t-slots. 6' [1.8m] (7712ULBC20R, 7712ULBC20R-TL* 7712ULBC20R-TL) or 15' [4.6m] 7712ULBD20R-TL* (7712ULBD20R, 7712ULBD20R-TL) cord. Length 77" [2m]. Receptacle center-to-center 6" [152mm]. Units available with straight blade or NEMA L5-20P locking plug. 7011ULBC20R/ c(UL)us 7011ULBD20R * Use "TL" suffix with Catalog Number for locking plug.



20A NEMA L5-20P Locking Plug

7712ULBC20R/ 7712ULBD20R

Compact Plug-In Outlet Centers Ordering Information **Description/Specifications** Catalog No./Item Catalog No./Item UL100BC UL207BC Compact Plug-In Outlet Center -UL100BD Five outlets, 6' [1.8m] (UL100BC) or UL207BD 15' [4.6m] (UL100BD)cord. Length 9 1/4" [235mm]. Receptacle centerto-center 1 1/4" [32mm]. UL101BC Compact Plug-In Outlet Center -**UL101BD** Four outlets, 6' [1.8m] (UL101BC) or **UL218BC** 15' [4.6m] (ÚL101BD) cord. Length **UL218BD** 9 1/4" [235mm]. Receptacle centerto-center1 1/4" [32mm]. UL104BC Compact Plug-In Outlet Center -UL104BD Four outlets, lighted switch. 6' [1.8m] (UL104BC) or 15' [4.6m] (104BD) UL210BC cord. Length 9 1/4" [235mm]. UL210BD Receptacle center-to-



Compact Plug-In Outlet Center -Seven outlets, lighted switch. 6' [1.8m] (UL204BC) or 15' [4.6m] (UL204BD) cord. Length 13" [330mm]. Receptacle center-tocenter 1 1/4" [32mm]. c(UL)us

center 1 1/4" [32mm].




Compact Plug-In Outlet Center -Eight outlets, 6' [1.8m] (UL205BC) or 15' [4.6m] (UL205BD)cord. Length 13" [330mm]. Receptacle center-tocenter 1 1/4" [32mm]. c(UL)us



Compact Plug-In Outlet Center -Six outlets. 6' [1.8m] (UL206BC) or 15' [4.6m] (UL206BD)cord. Length 12 1/4" [311mm]. Receptacle centerto-center 1 1/4" [32mm].




c(UL)us





Compact Plug-In Outlet Center -Six outlets, lighted switch. Putty white finish, 6' [1.8m] (R610) or 15' [4.6m] (R612) cord. Length 12 1/4" [311mm]. Receptacle center-tocenter 1 1/4" [32mm].





Compact Plug-In Outlet Center -Six outlets, lighted switch. Putty white finish, plastic housing. 6' [1.8m] or 15' [4.6m] cord. Length 12' [305mm]. Receptacle center-tocenter 1 1/4" [32mm].






20A Plug-In Outlet Centers Ordering Information Catalog No./Item **Description/Specifications** Catalog No./Item **Description/Specifications ULB420-6** 20A Plug-In Outlet Center - Four **ULB820-6** 20A Plug-In Outlet Center - Eight 20A, 120V, 60Hz 2500 watt outlets. ULB420-15 ULB820-15 20A, 120V, 60Hz 2500 watt outlets. Lighted switch, putty white finish. Lighted switch, putty white finish. 6' [1.8m] (ULB420-6) or 15' [4.6m] 6' [1.8m] (ULB820-6) or 15' [4.6m] (ULB420-15) cord. Length 10 3/4" (ULB820-15) cord. Length 17 1/4" [273mm]. Receptacle center-to-[438mm]. Receptacle center-tocenter 1 1/2" [38mm]. center 1 1/2" [38mm]. c(VL)us **ULB620-6** 20A Plug-In Outlet Center - Six ULB620-15 20A, 120V, 60Hz 2500 watt outlets. Lighted switch, putty white finish. 6' [1.8m] (ULB620-6) or 15' [4.6m]


c(UL)us


(ULB620-15) cord. Length 13 1/4" [337mm]. Receptacle center-to-


center 1 1/2" [38mm].



	Industrial Plug-In Outlet C
Catalog No./Item	Description/Specifications
UL2064BC UL2064BD	Industrial Plug-In Outlet Center – Twelve outlets, lighted switch. 6' [1.8m] (UL2064BC) or 15' [4.6m] (UL2064BD) cord. Length 72" [1830mm]. Receptacle center-to- center 5 1/4" [133mm].
	c (UL) us







International Plug-In Outlet Center Ordering Information Description/Specifications IEC5 International Plug-In Outlet Center – Five 250V, IEC 320 outlets. Gray finish. 10A single pole circuit breaker. Power cord not included. Length 11" [279mm]. Receptacle center-to-center 1 1/2" [38mm]. TÜV and UL1950 Information Technology Listed.

Steel Cord-Ended Plugmold Ordering Information			
Catalog No./Item	Description/Specifications		
V20-C2 G20-C2	Steel Cord-Ended Plugmold – Six outlets, ivory or gray finish. 6' [1.8m] cord. Length 40" [1m]. Receptacle center-to-center 6" [152mm].		
(h) (b			

	Nonmetallic Cord-Ended Plugmold Ordering Information		
Catalog No./Item	Description/Specifications		
NM20-C3	Nonmetallic Cord-Ended Plugmold – Six (3 duplex) outlets, ivory finish. 6' [1.8m] cord. Length 36" [915mm]. Receptacle center-to-center 12" [305mm].		
c UL us	₽		
NM20-C4	Nonmetallic Cord-Ended Plugmold – Eight (4 duplex) outlets, ivory finish. 6' [1.8m] cord. Length 48" [1.2m]. Receptacle center-to-center 12" [305mm].		
c UL us			

Questions? Call Technical Support today at 1-800-SENTREX.



60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295-3472)
www.legrand.us/wiremold
570 Applewood Crescent
Vaughan, Ontario L4K 4B4
Phone: 905.738.9195

