

## Eaton 10250T pushbutton

10250T197LRP24

UPC:782114710814

### Dimensions:

- **Height:** 2 IN
- **Length:** 2.1 IN
- **Width:** 2 IN

**Weight:** .25 LB

### Warranties:

- 1 year

### Specifications:

- **Type:** Heavy-Duty Watertight/Oiltight
- **Actuator:** Standard
- **Light Unit Type:** LED, full voltage
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Lens Color:** Red
- **Lens Material:** Plastic
- **Light Unit Voltage:** 24 Vac/dc
- **Series:** 10250T
- **Style:** 30.5 mm

### Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T197LRP24](#)

### Certifications:

- UL Listed
- CSA Certified

### Product compliance:

- CE Marked

