

Eaton 10250T pushbutton

10250T197LGP24

UPC:782114710821

Dimensions:

- **Height:** 3.2 IN
- **Length:** 2.4 IN
- **Width:** 2.1 IN

Weight:.4 LB

Warranties:

- 1 year

Specifications:

- **Type:** Heavy-Duty Watertight/Oiltight
- **Actuator:** Standard
- **Light Unit Type:** LED, full voltage
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Lens Color:** Green
- **Lens Material:** Plastic
- **Light Unit Voltage:** 24 Vac/dc
- **Series:** 10250T
- **Style:** 30.5 mm

Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T197LGP24](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked

