

## Eaton SVX adjustable frequency drive

**SVX025A1-4A1B1**

**UPC:**782116011520

### **Dimensions:**

- **Height:** 11.7 IN
- **Length:** 9.3 IN
- **Width:** 7.6 IN

**Weight:**40.8 LB

### **Warranties:**

- 2 year

### **Specifications:**

- **Brake Chopper:** Brake chopper
- **Input:** Three-phase, EMC H
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR6
- **Horsepower:** 25 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 480 V

### **Supporting documents:**

- [SVX9000 Adjustable Frequency Drives Brochure](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [Product Datasheet - SVX025A1-4A1B1](#)
- [SVX\\_\(FR6\) AutoCAD 2D Footprint \(mm\)](#)
- [SVX\\_\(FR6\) 2D Drawing Xchange](#)
- [SVX\\_\(FR6\) 3D Inventor](#)
- [SVX\\_\(FR6\) AutoCAD 2D Footprint](#)
- [SVX\\_\(FR6\) 3D Model Xchange](#)
- [SVX\\_\(FR6\) 2D PDF](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [9000X AFD User Manual](#)



- [SVX9000 Adjustable Frequency Drives Product Aid](#)
- [Eaton Specification Sheet - SVX025A1-4A1B1](#)

**Certifications:**

- UL 508C
- IEC 61800-2
- EN 61800-3 Level H

**Product compliance:**

- Contact Manufacturer