

Eaton SVX adjustable frequency drive

SVX015A1-4A1B1

UPC:782116011506

Dimensions:

- **Height:** 16.5 IN
- **Length:** 8.4 IN
- **Width:** 5.6 IN

Weight:17.9 LB

Warranties:

- 2 year

Specifications:

- **Brake Chopper:** Brake chopper
- **Input:** Three-phase, EMC H
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR5
- **Horsepower:** 15 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 480 V

Supporting documents: No Data

Certifications:

- EN 61800-3 Level H
- UL 508C
- IEC 61800-2

Product compliance:

- Contact Manufacturer

