



Eaton SVX adjustable frequency drive

SVX050A1-4A1N1

UPC:782116011551

Dimensions:

- **Height:** 16 IN
- **Length:** 29.75 IN
- **Width:** 14.5 IN

Weight:79.8 LB

Warranties:

- 2 year

Specifications:

- **Brake Chopper:** No brake chopper
- **Input:** Three-phase, EMC H
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR7
- **Horsepower:** 50 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 480 V

Supporting documents:

- [SVX9000 Adjustable Frequency Drives Brochure](#)
- [Product Datasheet - SVX050A1-4A1N1](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [SVX_\(FR7\) 3D Model Xchange](#)
- [SVX_\(FR7\) AutoCAD 2D Footprint \(mm\)](#)
- [SVX_\(FR7\) 3D Inventor](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [SVX_\(FR7\) 2D PDF](#)
- [SVX_\(FR7\) 2D Drawing Xchange](#)
- [SVX_\(FR7\) AutoCAD 2D Footprint](#)
- [9000X AFD User Manual](#)

- [SVX9000 Adjustable Frequency Drives Product Aid](#)
- [Eaton Specification Sheet - SVX050A1-4A1N1](#)

Certifications:

- IEC 61800-2
- UL 508C
- EN 61800-3 Level H

Product compliance:

- Contact Manufacturer