

## Eaton SVX adjustable frequency drive

**SVX150A1-4A1N1**

**UPC:**782116094172

**Dimensions:**

- **Height:** 45.3 IN
- **Length:** 13.4 IN
- **Width:** 18.9 IN

**Weight:**321.9 LB

**Warranties:**

- 2 year

**Specifications:**

- **Brake Chopper:** No brake chopper
- **Input:** Three-phase, EMC H
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR9
- **Horsepower:** 150 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 480 V

**Supporting documents:**

- [SVX9000 Adjustable Frequency Drives Brochure](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [Product Datasheet - SVX150A1-4A1N1](#)
- [SVX\\_\(FR9\) 2D Drawing Xchange](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [SVX\\_\(FR9\) 2D PDF](#)
- [SVX\\_\(FR9\) AutoCAD 2D Footprint \(mm\)](#)
- [SVX\\_\(FR9\) AutoCAD 2D Footprint](#)
- [SVX\\_\(FR9\) 3D Inventor](#)
- [SVX\\_\(FR9\) 3D Model Xchange](#)
- [9000X AFD User Manual](#)



- [SVX9000 Adjustable Frequency Drives Product Aid](#)
- [Eaton Specification Sheet - SVX150A1-4A1N1](#)

**Certifications:**

- EN 61800-3 Level H
- UL 508C
- IEC 61800-2

**Product compliance:**

- Contact Manufacturer