

Eaton SVX adjustable frequency drive

SVX020A1-4A1B1

UPC:782116011513

Dimensions:

- **Height:** 22 IN
- **Length:** 9.3 IN
- **Width:** 7.6 IN

Weight:40.8 LB

Warranties:

- 2 year

Specifications:

- **Brake Chopper:** Brake chopper
- **Input:** Three-phase, EMC H
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR6
- **Horsepower:** 20 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 480 V

Supporting documents:

- [SVX9000 Adjustable Frequency Drives Brochure](#)
- [Product Datasheet - SVX020A1-4A1B1](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [SVX_\(FR6\) 2D Drawing Xchange](#)
- [SVX_\(FR6\) 3D Model Xchange](#)
- [SVX_\(FR6\) 3D Inventor](#)
- [SVX_\(FR6\) AutoCAD 2D Footprint](#)
- [SVX_\(FR6\) 2D PDF](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [SVX_\(FR6\) AutoCAD 2D Footprint \(mm\)](#)
- [9000X AFD User Manual](#)



- [SVX9000 Adjustable Frequency Drives Product Aid](#)
- [Eaton Specification Sheet - SVX020A1-4A1B1](#)

Certifications:

- EN 61800-3 Level H
- UL 508C
- IEC 61800-2

Product compliance:

- Contact Manufacturer