

## Eaton SVX adjustable frequency drive

**SVX030A1-4A1B1**

**UPC:**782116011537

**Dimensions:**

- **Height:** 11.8 IN
- **Length:** 25 IN
- **Width:** 10.5 IN

**Weight:**43.85 LB

**Warranties:**

- 2 year

**Specifications:**

- **Brake Chopper:** Brake chopper
- **Input:** Three-phase, EMC H
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR6
- **Horsepower:** 30 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 480 V

**Supporting documents:** No Data

**Certifications:**

- IEC 61800-2
- UL 508C
- EN 61800-3 Level H

**Product compliance:**

- Contact Manufacturer

