



FOR PRODUCT VIDEOS, DEMONSTRATIONS AND MORE, SCAN THIS QR CODE OR VISIT:

www.youtube.com/GreenleeDEMO

WWW.GREENLEE.COM

SAVE TIME AND MONEY WITH EVERY PULL



G3 Tugger™

ORDERING INFORMATION

CAT NO.	UPC NO.	DESCRIPTION
G3	00905	G3 Tugger (Pkgd)
578	31910	Clevis Assy, Grip-Kellems
39106	39106	Swivel
30550	30550	Lt Duty Pulling 33-03-018 Grip
39905	39905	Connector Unit-Rope 5,000#
455	23774	Rope, Poly Braid/Braid (1/2 X 300)
456	23777	Rope, Poly Braid/Braid (1/2 X 600)
644	15316	Stand-Rope Reel
650	15324	Sheave, Cable 6" Hook Type
651	15325	Sheave, Cable 12" Hook Type

CAT NO.	UPC NO.	DESCRIPTION
652	15326	Sheave-Cable 18" Hook Type
653	15327	Sheave-Cable 24" Hook Type
683	15372	Jackstand Assy, Reel
684	15375	Spindle, Reel Stand (76")
6810	05564	Feeder Assembly, Cable
444	01874	Foot Switch Unit



www.greenlee.com MA6001 08/13

4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070

©2013 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA

Greenlee Textron Inc. is a subsidiary of Textron Inc.



GREENLEE
A Textron Company

G3 Tugger™

VERSATILE

Can hook on the back of a truck hitch



FASTER

- 20% faster cable pulls*
- High-speed pulls up to 1,000 lbs.

STRONGER

- 25% stronger continuous pulling load*
- Durable motor designed for pulling efficiency

EASIER

- 3X faster setup*
- No loose pieces

+ No load

* When compared to competitive models



DEPENDABLE

Customized motor with circuit breaker specifically designed for cable pulling

ADJUSTABLE

Patented clamp easily adjusts for different sizes of conduit

SAFE

Right angle sheave keeps operators safely out of direct line of pulls

EASY

Change tail length, pull direction, and angle of pull with ease

QUICK

Dual capstan pulls:
– High Speed (97 ft/min)+
– Low Speed (41 ft/min)+

PULLING FORCE

Continuous rating: 1,200 lbs.
Intermittent rating: 2,000 lbs.

PORTABLE

Handle and wheels increase mobility around jobsites

