
### Stainless steel sealing ring



### Polycarbonate sealing ring

Cat. no.	Description
S102WD	Ring, available with any meter socket

When ordering any meter socket, add suffix "Z" to meter socket cat. no. to exchange standard stainless steel ring for \$102WD model.



# Meter protectors

### **Product specifications**

- Meter protector for use in problem areas (trailer parks, playgrounds, conservation areas)
- Steel construction (16 ga. galv. steel)
- Clear, unbreakable polycarbonate front cover, which allows full view of meter revenue reading and serial number
- Sealing and padlocking provision
- · Grey painted

Cat. no.	Description
MP01	71/6 in. dia. x 43/4 in. deep for use with single-phase residential meters
MP02	71/6 in. dia. x 83/4 in. deep for use with all meters, other than single-phase residential meters

#### Blank meter cover plates

Description	Cat. no.	
Grey ABS	BS087	
Plastic "throw-away" cover	BS089	
Clear unbreakable polycarbonate	BS090	

Not recommended as a permanent cover for energized meter sockets.

#### Jumper bar



Cat. no. Description
CM-BS100 200 A max.

### Mast coupler



Cat. no. Description

MH200

Fits all sockets with regular 2½ in. hub opening

### Mast hubs



	Cat. no.	PVC cat. no.	A hub size (in.)	В	
MH10X	MH10X	_	1	For 2½ in. regular hub opening (add hub adapter pla	
	MH12X	E991G	11/4	BS052 if used with units having 4 in. hub openings)	
	MH15	E991H	11/2		
	MH20	E991J	2		
	MH25	E991K	21/2		
	MH30	E991L	3	For 4 in. hub opening	
	MH35	<del>-</del>	3½		
	MH40	_	4	Diagram B B	



ACCESSORIES D59

# Accessories

### Hub adapter plate



Cat. no.	Description
BS052	Permits use of regular size hubs on larger hub openings



Hub opening closure plates



Cat. no.	Description
BS051	Inside attachment for regular hub opening (i.e. 1 in. to 2½ in.)
BS054	Inside attachment for larger hub opening (i.e. 3 in. to 4 in.)

Insulated neutral kits



	Cat. no.	Description
	IN1000BA, IN1000BE, IN1000PL	100 A Max.
	IN2000BS, IN2000PL	200 A Max.

Specify socket when ordering.




### Insulated neutral kit



Cat. no.	Description
IN40003S	400 A Max. (JS4)

### Ground lug on neutral kit



### Identification marker kits

	Cat. no.	Description	Markers Kit Includes	Qty.
MINI-ID-KIT MICRO-ID-KIT	Plastic case	Stainless steel markers of each numbers 0 through 9 (dash + service)	10	
	MICRO-ID-KIT	Blue metal	Stainless steel markers of each letters A through D	10
		carrying case	Stainless steel markers of each numbers 0 through 9	10
		_	Word "SERVICE"	10
		_	CM-BS100 Jumper bar 200 A max.	4
			LS500 Meter jaw safety shroud	10


### Identification markers


	Cat. no.	Description
3 0 1  Consist of thermoplastic insulators with jaws and connectors assembled	No. 0 through No. 9 No. A through No. Z No. SERVICE	Clipped to the upper lip of the enclosure; provides permanent customer identification packed and sold in polyethylene bags of 10 identical markers except "SERVICE" which has 7 individual letters
for replacement of one meter socket		

ACCESSORIES D61


# Accessories

Ready-to-install replacement block assemblies










Cat. no.	Description
BS2-XBGN-UNI	Neutral 200 A



# Repair kits

#### Replacement part kits

	Ca
REPAIR KIT BQ2-VGN	RE
	RE
	RE
	RE
	RE
The second	RE
THE STATE OF THE S	

Cat. no.	For meter socket	Components*
REPAIR KIT BE1-TCV	BE1-TCV	BS2027, CDA110, BONDLUG2, SCREW-BS1002
REPAIR KIT BQ2-V	BQ2-V	BS2027, BS2611L, BONDLUG2, SCREW-BS2402
REPAIR KIT BQ2-VGN	BQ2-VGN	BS2027, BS2411GN, BONDLUG2, SCREW-BS2402
REPAIR KIT BS2-TCV	BS2-TCV	BS2027, BS2611L, BONDLUG2, SCREW-BS2402
REPAIR KIT BS2-TCVBC	BS2-TCVBC	BS2027, BS2611L, NA75Z-3, SCREW-BS2402
REPAIR KIT MO2V/VO	MO2V/VO	BS2027, BS8608, BONDLUG2, SCREW-BS2402

Easy to reorder. Simply add suffix -FG to the components listed in the kit.

### **Bond lug**

	Cat. no.	Description
000 000	BONDLUG2-FG	Bond lug to be used in BE1, BQ2, BS2, MO2–
50 12	NA75Z-3-FG	Bond lug to be used in BS2-TCVBC

### Neutral lug

	Cat. no.	Description
	BS8608-FG	Neutral for MO2 200 A
1000	CDA110-FG	Neutral for BE1 100 A

### Shroud

	Cat. no.	Description
\$	BS2027-FG	Red meter jaw safety shroud

#### Set screw

		Cat. no.	Description
0		SCREW-BS1002-FG 100A	Set screw only for 100 A lugs
U	0	SCREW-BS2402-FG 200A	Set screw only for 200 A lugs

#### Neutral

	Cat. no.	Description
ole D	BS2611L-FG	Neutral 200 A
	BS2411GN-FG	Neutral 200 A, comes with ground

<sup>\*</sup> Each part comes in a bag of 10.

ACCESSORIES D63

# Accessories

#### Fifth jaw assemblies



		Standard capacity 9 o'clock position		Full capacity 9 o'clock position	Full capacity 6 o'clock position
	Meter socket series	C205	Z105*	Z205*	CM-B106*
	BA3	•	•		
	BDC	•		•	
T. A.	BE1	•	•		•
9	BE2	•	•		
	BEC	•	•		
	BD2	•		•	
	BQ2	•		•	
	BS2 / BS2L	•		•	
	BS4 / BSC4	•		•	
	CO1	•	•		•
	CO2	•		•	
	CO1 Multigang	•	•		•
	JS4B	•			

<sup>\*</sup> CSA not applicable

\_

#### Pole mount bracket kit

	Cat. no.	Description	Conductor range (AWG)	Use with series	Option 1	Option 2
***	РМВ200	Secures Microlectric meter socket to a wooden pole via option 1 or 2	14-2	BA3, BE1, BQ2, BS, CL, CO1, CO2, CT, MO2, PL17, PL27, VT	Use a lag bolt through ⅓ in. center keyhole	Use the two side bracket mounting holes (0.320 in. dia.) to wrap around the pole

Suitable for any Microlectric meter socket with mounting holes 5 in. apart. Attach meter socket using one or two bracket(s). PMB200 kit comes complete with 2 brackets, 1 ground connector. Includes assembly hardware.


### Pole mounting kit

				Weight	
	Cat. no.	Kit includes	lb	kg	Qty
01	PMBJS4	Support hangers	9.03	4.09	ž
9101	_	⅓ in. x 4 in. lag bolt	_	_	1
		¾ in. x 3 in. lag bolt	_	-	4
		5∕16 in. x 1 in. carriage bolts, nuts and lock washers	-	-	_
0	PMB6X12	6 in. offset from pole c/w 12 in. strut	7.7	3.5	1
	PMB6X24	6 in. offset from pole, comes with 24 in. strut	9.2	4.2	1
	PMB9X12	9 in. offset from pole, comes with 12 in. strut	9.2	4.2	
	PMB9X24	9 in. offset from pole, comes with 24 in. strut	11.0	5.0	

### Pole line hardware

					,		Weight (100 p			ics)	
Cat. no.	Description	F dia. (in.)	G dia. (in.)	H dia. (in.)	T thick (in.)	lb	kg	Std. pkg.			
RC729	Square washer	5/8	2	-	3/16	22	10.0	400			
BC301L	Carriage bolt	3/8	1½	11/2	_	11	5.0	50			
BO506	Oval eye bolt	5/8	6	3	_	122	55.4	50			
BO508	Oval eye bolt	5/8	8	4	-	136	61.8	50			
BO510	Oval eye bolt	5/8	10	4	-	150	68.1	50			
BO512	Oval eye bolt	5/8	12	4	-	168	76.3	50			

### Diagrams



ACCESSORIES D65

# Accessories

#### — Breaker mounting bracket

	Cat. no.	Description
	CO3517M-FG	Adjustable mounting bracket for CO2 series to adapt to Siemens, Square D and Eaton breakers
e braid and co	onductor kits	
	Cat. no.	Description
	CO2FB-KIT	Connection wire adaptor kit for CO2 series meter sockets for field installation to be used with Cutler Hammer breakers
	CO3009-KIT	Siemens type "QR" breaker conductor kit (breakers not included)
	CO3009SD-KIT	Square D breaker conductor kit (breakers not included)
	CO3409FB-KIT	Eaton breaker flexible braid kit (breakers not included)
	CO3009A2-KIT	ABB breaker conductor kit (breakers not included)
	CO1009A1-KIT	ABB Breaker conductor kit for 100 A type A1A

### — Breakers

	Cat. no.	Description
	A1A100TL2TNB-FG	ABB 100 A 10 kA breaker
	A1N100TL2TNB-FG	ABB 100 A 22 kA breaker
00	A2A125TL2TNB-FG	ABB 125 A 10 kA breaker
700	A2A150TL2TNB-FG	ABB 150 A 10 kA breaker
700	A2A200TL2TNB-FG	ABB 200 A 10 kA breaker
700	A2N125TL2TNB-FG	ABB 125 A 22 kA breaker
00	A2N150TL2TNB-FG	ABB 150 A 22 kA breaker
7	A2N200TL2TNB-FG	ABB 200 A 22 kA breaker

#### Connector kit

Cat. no.	Description
BP250	Connector kit 2 x 250 kcmil
WE . 100	
India	