


Steel City

NOTE: GFCI COVER AND RECEPTACLE SHOWN



FEATURES:

1. FACEPLATE COUPLING MADE FROM A HIGH STRENGTH ZINC ALLOY.
2. P64 SERIES COVERS FOR GFCI OR DUPLEX RECEPTACLES.
3. STEEL FLOOR BOX, 18.0 CU. INCH CAPACITY WITH (2) 1/2" K.O.'S ON EACH SIDE, (1) 1/2" K.O. AND (2) CABLE K.O.'S WITH NONMETALLIC SHEATHED CABLE CLAMPS EACH END AND (1) K.O. ON BOTTOM. COMES WITH 12 A.W.G. INSULATED COPPER GROUNDING WIRE PIGTAIL.
4. FOR USE WITH HARDWOOD, CERAMIC TILE AND CARPET FLOORS.
5. GFCI AND DUPLEX RECEPTACLES ARE RATED AT 15AMP 125V AND PROVIDED WITH A WHITE FACE.

CAT NO.	** DESCRIPTION
71W-DS-C	FLOOR BOX W/GROUND WIRE, BRS, DUPLEX COVER
71W-GFCI-C	FLOOR BOX W/GROUND WIRE, BRS, GFCI COVER
71W-DS-N-C	FLOOR BOX W/GROUND WIRE, NKL, DUPLEX COVER
71W-GFCI-N-C	FLOOR BOX W/GROUND WIRE, NKL, GFCI COVER

** BRS - BRASS PLATE
NKL - NICKEL PLATED

NOTE:
MINIMUM 3/8 INCH FINISHED FLOOR THICKNESS



GENERAL NOTES

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.

REVISIONS

- | | |
|---|---|
| 1 | SEE ERN (2006105) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: UD55559 |
|---|---|

Thomas & Betts
www.tnb.com

DESCRIPTION: **71W SERIES SINGLE GANG W/ GROUND WIRE RESIDENTIAL FLOOR BOX**

ORIGINAL PROJECT NO / (ERN NO)	SHEET NO:	REV. NO:	DRAWING NO:
UD55559 / (2005756)	1 OF 1	1	WSD-000184