Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding Acceptor® Hazardous Location Receptacles



Ordering Information

Listed to UL Standard 498

Description Explosion Proof, Receptacle with Adapter, Single Pack Device Color UPC Metallic 783585412504

Catalog Number 4 UGRO20231



Resources

eCatalog

Performance

Electrical

Listings

Current Interrupting C Dielectric Voltage W

Certified for current interrupting at full rated current Withstands 2,000V minimum

Mechanical

Product Identification Terminal Accommodation Terminal Identification

Ratings are a permanent part of the device #14-#10 AWG copper stranded or solid conductor only Terminals identified in accordance with UL 498 and CSA

 Environmental

 Flammability
 UL 94 V2 or better

 Operating Temperatures
 Maximum continuous 75°C; minimum -40°C (w/o impact)

