

## Eaton definite purpose contactor

**C25FNF360B**

**UPC:**782113476148

### **Dimensions:**

- **Height:** 3.75 IN
- **Length:** 3.97 IN
- **Width:** 2.63 IN

**Weight:**2.8 LB

**Notes:**Resitive Load rating per pole

### **Warranties:**

- 1 year

### **Specifications:**

- **Connection:** Quick
- **Amperage Rating:** 60A
- **Coil:** 208-240 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 15-50A, two- and three-pole
- **Model:** Contactor
- **Number Of Poles:** Three-pole
- **Resistive Load:** 75A
- **Terminals:** Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
- **Type:** Non-reversing

### **Supporting documents:**

- [Eaton's Volume 5-Motor Control and Protection](#)
- [C25FNF3 AutoCAD 2D Footprint \(mm\)](#)
- [C25FNF3 3D Model Xchange](#)
- [C25FNF3 3D Inventor](#)
- [C25FNF3 2D PDF](#)
- [C25FNF3 AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - C25FNF360B](#)

### **Certifications:**

- CSA Certified



- UL Recognized

**Product compliance:**

- RoHS Compliant

---

© 2016 Eaton. All rights reserved.