

Eaton 10250T pushbutton

10250T411

UPC:782113203713

Dimensions:

- **Height:** 3.4 IN
- **Length:** 2.4 IN
- **Width:** 2.1 IN

Weight: .35 LB

Warranties:

- 1 year

Specifications:

- **Application:** Pushbutton
- **Special Features:** 10250T series
- **Type:** 30.5 mm Heavy-Duty Watertight/Oiltight
- **Bezel:** Chrome
- **Illumination:** Illuminated
- **Led Lamp Number:** #755
- **Light Unit Type:** Incandescent, transformer
- **Light Unit Voltage:** 120 Vac
- **Mounting:** Flush
- **Operating Mode:** Momentary
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T411](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:

- CE Marked



