

## Eaton E50 NEMA heavy duty plug-in limit switch

E50AT3

UPC:782113308821

### Dimensions:

- **Height:** 2 IN
- **Length:** 5 IN
- **Width:** 2.25 IN

**Weight:**1.146 LB

### Warranties:

- 1 year

### Specifications:

- **Type:** Assembly
- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 240 Vac, 1A at 250 Vdc
- **Accessories:** E50DT3
- **Actuator:** Top push roller, spring return
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Maximum Ac Current:** 10A continuous
- **Maximum Dc Current:** 1A
- **Operating Temperature:** 14° to 201°F (-10° to 94°C)
- **Series:** E50

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50AT3](#)

### Certifications:

- CSA Certified
- UL Listed

**Product compliance:** No Data



