

Eaton XT IEC contactor

XTCE025C10E

Dimensions:

- **Height:** 3.898 IN
- **Length:** 3.425 IN
- **Width:** 1.85 IN

Weight:.9 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 25A
- **Coil Voltage:** 208 Vac, 60 Hz
- **Contact Configuration:** 1NO
- **Frame Size:** 45 mm
- **Frequency Rating:** 60 Hz
- **Max Hp Rating:** 2, 3, 5/ 7.5, 10, 15, 20 hp
(1/3PH @115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE_C 3D Model Xchange](#)
- [XTCE_C 2D PDF](#)
- [XTCE_C AutoCAD 2D Footprint](#)
- [XTCE_C 2D Drawing Xchange](#)
- [Global Data Sheet - XTCE025C10E](#)
- [Eaton Specification Sheet - XTCE025C10E](#)

Certifications:

- IEC 60947
- CSA Certified



- UL Listed
- EN 60947

Product compliance:

- RoHS Compliant
- CE Marked

© 2016 Eaton. All rights reserved.