

Eaton XT IEC contactor

XTCE225H22A

Dimensions:

- **Height:** 8.5 IN
- **Length:** 10 IN
- **Width:** 6 IN

Weight:6.5 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties: No Data

Specifications:

- **Amperage Rating:** 225A
- **Coil Voltage:** 100 Vac 50 Hz, 120 Vac, 60 Hz
- **Contact Configuration:** 2NO-2NC
- **Frame Size:** 140 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 50, 75, 150, 200 hp (3PH
@200,240,480,600 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE_H 3D Model Xchange](#)
- [XTCE_H 2D Drawing Xchange](#)
- [XTCE_H 3D Inventor](#)
- [XTCE_H 2D PDF](#)
- [XTCE_H AutoCAD 2D Footprint \(mm\)](#)
- [XTCE_H AutoCAD 2D Footprint](#)
- [Global Data Sheet - XTCE225H22A](#)
- [Eaton Specification Sheet - XTCE225H22A](#)

Certifications:

- UL Listed



- CSA Certified
- IEC 60947
- EN 60947

Product compliance:

- CE Marked
- RoHS Compliant

© 2016 Eaton. All rights reserved.