

Residual Current Operated Circuit Breakers

167109

Dimensions:

- **Height:** 3 IN
- **Length:** 3 IN
- **Width:** 3.5 IN

Weight: .3 LB

Notes: Additionally protects against special forms of residual pulsating DC which have not been smoothed.

Warranties: No Data

Specifications:

- **Type:** Type G/A
- **Amperage Rating:** 63A
- **Number Of Poles:** Four-pole
- **Circuit Protection:** 30 mA residual protection

Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [UL 1053 DIN Rail RCCB](#)
- [Eaton Specification Sheet - 167109](#)

Certifications:

- UL 1053
- IEC 61008
- EN 61008

Product compliance: No Data

