

Programmable controller

XV-152-D6-10TVRC-10

Dimensions:

- **Height:** 6.131 IN
- **Length:** 8.332 IN
- **Width:** 2.083 IN

Weight:2.9 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Metal housing
- **Bezel:** Blank front
- **Display Size:** 10.4 in
- **Fieldbus Type:** CANopen

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XV and XP Series Operator Interfaces Product Aid - PA04801003E](#)
- [Eaton Specification Sheet - XV-152-D6-10TVRC-10](#)

Certifications:

- UL Listed
- cUL Listed

Product compliance:

- RoHS Compliant
- CE Marked

