


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
NK6XPP24P	.85 LB/10 PCS (383.6 g/EACH PC)

- NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
 3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
 4. THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
 5. USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
 6. PART INCLUDES:
 - 1-PATCH PANEL ASSEMBLY
 - 4-LABEL COVERS
 - 4-LABELS
 - 1-SCREW KIT (INCLUDES FOUR (4) #12-24 SCREWS)
 - 1-SCREW KIT (INCLUDES FOUR (4) M6 SCREWS)
 - 24-RETENTION CAPS
 7. RETENTION CAPS ARE PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.
 8. LABELS ARE PRE-NUMBERED (1-24 WITH BLANK SIDE FOR CUSTOM LABELING)



PART NUMBER		SEE CHART	
TITLE			
NETKEY 24 PORT ALL MOLDED CATEGORY 6A PUNCHDOWN PATCH PANEL			
CUSTOMER DRAWING			
ITEM REVISION NAME		10M163AG/01	
DATASET FILE NAME		10M163AG_DC02/01A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ± .1 [2.54] .xxx ± .005 [.127]		BASE-REINFORCED PBT COVER-ABS	
.xx ± .01 [.25] ANGLES ± 5 °		DRAWING NUMBER:	
		10M163AG-02	
DRAWN BY	DATE	CHK	SCALE
BJN	2-4-15	MDJR	NONE
SHT 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	5-25-17	BJN	JAV	RWI	REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY	10M163AG-02

D10100DA/14