




TRIPPLE RECEPTACLE, TYPE DRC20-3
CODE: 077747




TRIPPLE SWITCH, TYPE TSC20-3
CODE: 077744




SINGLE SWITCH DOUBLE RECEPTACLE, TYPE TSDC20-3
CODE: 077746



BLANK, TYPE BRC20-3
CODE: 077748



DOUBLE SWITCH SINGLE RECEPTACLE TYPE DSDR20-3
CODE: 077745



PRODUCT CODE	PART NUMBER	A		B		C		D	
		(in)	(mm)	(in)	(mm)	(in)	(mm)	(in)	(mm)
077745	DSDR20-3	1.115	28.3	1.345	34.1	0.440	11.2	0.095	2.4
077747	DRC20-3	1.115	28.3	1.345	34.1			0.095	2.4
077744	TSC20-3	1.115	28.3			0.440	11.2	0.095	2.4
077746	TSDC20-3	1.115	28.3	1.345	34.1	0.440	11.2	0.095	2.4
077748	BRC20-3	1.115	28.3					0.095	2.4

PRODUCT CODE	PART NUMBER	E		H		L		W	
		(in)	(mm)	(in)	(mm)	(in)	(mm)	(in)	(mm)
077745	DSDR20-3	0.970	24.6	0.150	3.8	4.500	114.3	6.590	167.4
077747	DRC20-3			0.150	3.8	4.500	114.3	6.590	167.4
077744	TSC20-3	0.970	24.6	0.150	3.8	4.500	114.3	6.590	167.4
077746	TSDC20-3	0.970	24.6	0.150	3.8	4.500	114.3	6.590	167.4
077748	BRC20-3			0.150	3.8	4.500	114.3	6.590	167.4

PRODUCT CODE	PART NUMBER	t		SCREW CODE	GASKET CODE
		(in)	(mm)		
077745	DSDR20-3	0.125	3.1	172652 (4)	
077747	DRC20-3	0.125	3.1	172652 (4)	
077744	TSC20-3	0.125	3.1	172652 (4)	
077746	TSDC20-3	0.125	3.1	172652 (4)	
077748	BRC20-3	0.125	3.1	172652 (4)	072835 (1)