



PAT750LI

by Burndy
Catalog ID: PAT750LI

Prop 65 Notice

PATRIOT 12-Ton, C-Head, Hydraulic Self-Contained Battery Actuated Crimping Tool, 18V 3.0Ah Li-Ion, 120V AC Charger

- True, one-handed operation for advance, retract, and hold
- 12 ton output force
- State of the art crimping head design, 360° head rotation
- Ergonomically balanced tool design
- Durable High Impact Formed carrying case
- 5-year limited warranty on tool. 3-year warranty on battery and charger

Refined hydraulic system for ultra performance, speed and reliability, Field proven electronics for ultimate reliability in the harshest environments 5 year limited warranty, 3 year on batteries and charger, Lifetime warranty on INFINITY DRIVE®

Product Details

General

Application	Crimping
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	12 ton
Die Type	U DIE
Recharge Time	0.5 h
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810505175
UPC 12 Digit	7818105051755

Dimensions

Height	13.5 in
Jaw Width	1.65 in
Length	15.75 in
Weight	15.7 lb
Width	3.50 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 sol. - 750 kcmil; Aluminum: #8 sol. - 750 kcmil; ACSR: #4 AWG - 556.5 kcmil; Ground rods: 1/2"-1" diameter.
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, (2) 3Ah 18V li-ion batteries, charger, lanyard and case

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)