

## Eaton SVX adjustable frequency drive

**SVX040A1-4A1B1**

**UPC:**782116128495

### **Dimensions:**

- **Height:** 24.8 IN
- **Length:** 10.1 IN
- **Width:** 9.3 IN

**Weight:**77.2 LB

### **Warranties:**

- 2 year

### **Specifications:**

- **Brake Chopper:** Brake chopper
- **Input:** Three-phase, EMC H
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR7
- **Horsepower:** 40 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 480 V

### **Supporting documents:**

- [SVX9000 Adjustable Frequency Drives Brochure](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [Product Datasheet - SVX040A1-4A1B1](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [9000X AFD User Manual](#)
- [SVX9000 Adjustable Frequency Drives Product Aid](#)
- [Eaton Specification Sheet - SVX040A1-4A1B1](#)

### **Certifications:**

- IEC 61800-2



- EN 61800-3 Level H
- UL 508C

**Product compliance:**

- Contact Manufacturer

---

© 2016 Eaton. All rights reserved.