

Eaton M22 modular pushbutton

M22-L-Y

UPC:786685278650

Dimensions:

- **Height:** .45 IN
- **Length:** 1.17 IN
- **Width:** 1.17 IN

Weight:.085 LB

Notes:Includes contact block mounting adapter.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Indicating Light
- **Actuator:** Flush
- **Environmental Rating:** IP66, NEMA 4X, 13, Rk resistance 470
- **Size:** 22.5 mm
- **Button Color:** Yellow
- **Illumination:** Illuminated
- **Light Color:** White
- **Operating Cycles:** 100,000 Hours of operation
- **Series:** M22

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [M22-L 3D Inventor](#)
- [M22-L AutoCAD 2D Footprint \(mm\)](#)
- [M22-L 3D Model Xchange](#)
- [M22-L 2D Drawing Xchange](#)
- [M22-L AutoCAD 2D Footprint](#)
- [M22-L 2D PDF](#)



- [M22 Operators and Accessories](#)
- [M22 Pilot Devices](#)
- [Eaton Specification Sheet - M22-L-Y](#)
- [Global Data Sheet - M22-L-Y](#)

Certifications:

- CCC Marked
- CSA Certified
- Lloyd's Register Certified

Product compliance:

- Bureau Veritas
- CE Marked
- GoST-R