

Eaton E50 NEMA heavy duty plug-in limit switch

E50AR1

UPC:782113289861

Dimensions:

- **Height:** 2.46 IN
- **Length:** 4.22 IN
- **Width:** 1.54 IN

Weight:1.2 LB

Warranties:

- 1 year

Specifications:

- **Type:** Assembly
- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 240 Vac, 1A at 250 Vdc
- **Accessories:** E50DR1
- **Actuator:** Side rotary
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Maximum Ac Current:** 10A continuous
- **Maximum Dc Current:** 1A
- **Operating Temperature:** 10° to 200°F
- **Series:** E50 Heavy Duty Plug In

Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50AR1](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data



