

Eaton E50 NEMA heavy duty plug-in limit switch

E50SAN

UPC:782113290690

Dimensions:

- **Height:** 1.73 IN
- **Length:** 3.14 IN
- **Width:** 1.54 IN

Warranties:

- 1 year

Specifications:

- **Contact Rating:** 10A at 12 Vac, 1A at 125 Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Indicator:** Neon light
- **Light Unit Voltage:** 120 Vac
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Number Of Poles:** Single-pole
- **Operating Temperature:** -40° to 250°F (-40° to 121°C)
- **Series:** E50 Heavy Duty Plug In

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50SAN](#)

Certifications:

- UL Recognized
- CSA Certified

Product compliance: No Data

