

## Limit Switch Operator

**E50KL201**

**UPC:**782113290898

**Dimensions:**

- **Height:** .84 IN
- **Length:** 4.6 IN
- **Width:** .75 IN

**Warranties:**

- 1 year

**Specifications:**

- **Type:** Accessory
- **Size:** 0.32x0.33 in
- **Actuator:** Adjustable roller
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Material:** Nylatron
- **Operating Temperature:** 10° to 200°F
- **Series:** E50
- **Torque Rating:** 1.90 in-oz min. return
- **Used With:** Used with side rotary

**Supporting documents:**

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50KL201](#)

**Certifications:** No Data

**Product compliance:** No Data

