

## Limit Switch Operator

E50KL581

UPC:782113308753

### Dimensions:

- **Height:** .38 IN
- **Length:** 9.07 IN
- **Width:** 1.12 IN

### Warranties:

- 1 year

### Specifications:

- **Type:** Accessory
- **Actuator:** Adjustable rod
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Material:** Metal
- **Operating Temperature:** 10° to 200°F
- **Series:** E50
- **Torque Rating:** 2.2 in-oz min. return
- **Used With:** Used with side rotary

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50KL581](#)

**Certifications:** No Data

**Product compliance:** No Data

