

Eaton E50 NEMA heavy duty plug-in limit switch

E50ST

UPC:782113308814

Dimensions:

- Height: 3.13 IN
- Length: 1.54 IN
- Width: 1.78 IN

Weight:.3313 LB

Warranties:

- 1 year

Specifications:

- **Contact Rating:** 10A at 240Vac, 1A at 125Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Operating Temperature:** 14° to 250°F (-10° to 121°C)

Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50ST](#)

Certifications: No Data

Product compliance: No Data

