

Eaton E50 NEMA heavy duty plug-in limit switch

E50DD1

UPC:782113308876

Dimensions:

- **Height:** 2.46 IN
- **Length:** 1.05 IN
- **Width:** 1.54 IN

Warranties:

- 1 year

Specifications:

- **Type:** Limit Switch Head
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Operating Temperature:** 14° to 201°F (-10° to 94°C)
- **Series:** E50
- **Switch Type:** Two-step CW, CCW, or both, convertible

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50DD1](#)

Certifications: No Data

Product compliance: No Data

