

## Eaton E50 NEMA heavy duty plug-in limit switch

**E50BNR1**

**UPC:**782113344386

### **Dimensions:**

- **Height:** 4.22 IN
- **Length:** 1.54 IN
- **Width:** 2.46 IN

**Weight:**1.1063 LB

**Notes:**CW (clockwise) and CCW (counterclockwise) operation; easily convertible to CW only or CCW only operation

### **Warranties:**

- 1 year

### **Specifications:**

- **Accuracy:** Refer to installation publication P15836
- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 240Vac, 1A at 125Vdc
- **Contact Configuration:** 2NO-2NC
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Led Indicators:** Neon ( 120 Vac )
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Operating Temperature:** 10° to 201°F (-12° to 94°C)
- **Switch Type:** Side Rotary

### **Supporting documents:**

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50BNR1](#)

### **Certifications:**

- CSA Certified

- UL Listed

**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.