

## Eaton XT IEC contactor

### XTCE150G00A

#### Dimensions:

- **Height:** 6.69291339 IN
- **Length:** 6.2992126 IN
- **Width:** 4.37007874 IN

**Weight:** .5070632 LB

**Notes:** Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

**Warranties:** No Data

#### Specifications:

- **Amperage Rating:** 150A
- **Coil Voltage:** 110 Vac 50 Hz, 120 Vac, 60 Hz
- **Contact Configuration:** 0NO-0NC
- **Frame Size:** 90 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 10, 25, 30/ 40, 60, 125, 125 hp  
(1/3PH @ 115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

#### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE\\_G 3D Model Xchange](#)
- [XTCE\\_G 2D Drawing Xchange](#)
- [XTCE\\_G 2D PDF](#)
- [XTCE\\_G 3D Inventor](#)
- [XTCE\\_G AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - XTCE150G00A](#)
- [Global Data Sheet - XTCE150G00A](#)

#### Certifications:

- UL Listed
- CSA Certified



- IEC 60947
- EN 60947

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.