

Eaton XT IEC contactor

XTCE009B10TD

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes: Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Warranties: No Data

Specifications:

- **Amperage Rating:** 9A
- **Coil Voltage:** 24 Vdc
- **Contact Configuration:** 1NO
- **Frame Size:** 45 mm
- **Max Hp Rating:** 0.5, 1, 1.25/ 3, 3, 5, 7.5 hp (1/3PH @ 115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE_B 3D Model Xchange](#)
- [XTCE_B 3D Inventor](#)
- [XTCE_B 2D Drawing Xchange](#)
- [XTCE_B 2D PDF](#)
- [XTCE_B AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - XTCE009B10TD](#)
- [Global Data Sheet - XTCE009B10TD](#)

Certifications:

- UL Listed
- CSA Certified
- IEC 60947
- EN 60947



Product compliance:

- CE Marked
- RoHS Compliant

© 2016 Eaton. All rights reserved.